

**8000117002 PV combiner box thermal report****PV 124SXFXCXXV1O1TXPX15LWW****INPUT DATA**


Enclosure model	536 x 747 x 300 mm
Number of MPPT	12
Switch-disconnector model (per MPPT)	no switch-disconnector
Maximum current (per MPPT)	36 A
Number of inputs (per MPPT)	2
Fuse-link model	no fuse
Number of monitoring devices (per MPPT)	0
Type of mounting	Against wall, all other sides detached
Maximum allowed internal temperature	70 °C
Combined inputs	1
Height (A)	536 mm
Width (B)	747 mm
Depth (C)	300 mm
Effective cooling surface $A_e$ of the enclosure	1.16 m <sup>2</sup>

**RESULTS**

Ambient temperature (no direct sunlight)	35 °C
Rated current per input at 35°C	18.00 A
Power dissipated by components (except wiring)	0 W
Power dissipated by wiring	4 W
Total dissipated power	4 W
Temperature rise, mid height	2 °C
Temperature rise, top	2 °C
Internal temperature, top	37 °C

**CURRENT RATINGS**

At 35°C	18.00 A
At 40°C	18.00 A
At 45°C	18.00 A
At 50°C	18.00 A

**NOTES**

Thermal report based on IEC TR 60890 ed2.0

Thermal report does not include the direct sunlight effects