




[illegible]

- Todos los cables mñs cortos de 240mm se han de cortar a 240mm.

Additional product documents				1.				Tolerances: ISO 2768-mK			
				2.							
					Date	Name	Weidmüller				
				Drawn	08/06/2023	wm01276					
				Checked							
				Criterion for print			Description:				
				1 : 1		A3	PV 220S0F3CXXV0O0TA1PA15LWV				
				Customer:							
				WEIDMÜLLER, S.A.			Drawing-No / Material-No: 8000119550 drw Index 0 Sheet 1 / 5				
0		08/06/2023	wm01276	Customer-No:							
Index	Brief Description	Date	Name	104000066			Customer Description:				

WEIERGABE SOWIE Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster-, oder Geschmacksmusterrechte vorbehalten. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT AS WELL AS THE COMMUNICATION OF ITS CONTENTS TO OTHERS WITHOUT EXPLICIT AUTHORIZATION IS PROHIBITED. OFFENDERS WILL BE HELD LIABLE FOR THE PAYMENT OF DAMAGES AS WELL AS WEIDMÜLLER RESERVES THE RIGHT TO FILE FOR PATENTS, UTILITY MODELS OR DESIGNS. WEIDMÜLLER INTERFACE GmbH & Co. KG



Additional product documents				1.				Tolerances: ISO 2768-mK			
				2.							
				Drawn	Date	Name					
				Checked	08/06/2023	wm01276					
				Criterion for print			Description:				
				1 : 1		A3		PV 220S0F3CXXV0O0TA1PA15LWM			
				Customer:					Drawing-No / Material-No:		
				WEIDMÜLLER, S.A.							
				Customer-No:					drw Index	Sheet	
0		08/06/2023	wm01276	104000066					8000119550	0	2/5
Index	Brief Description		Date	Name		Customer Description:					

WEIDMÜLLER INTERFACE GmbH & Co. KG
WEIDMÜLLER SYSTEM reserves the right to file for patents, utility models or designs.
ZUWIDERHANDLUNGEN, VERFÄLSCHUNGEN, VERWERTUNG SEINES INHALTS SIND VERBOTEN, SOWEIT NICHT AUSDRUECKLICH GESTATET.
THE REPRODUCTION, DISTRIBUTION AND UTILISATION OF THIS DOCUMENT AS WELL AS THE COMMUNICATION OF ITS CONTENTS TO OTHERS WITHOUT EXPLICIT AUTHORIZATION IS PROHIBITED.
OFFENDERS WILL BE HELD LIABLE FOR THE PAYMENT OF DAMAGES.

	8	7	6	5	4	3	2	1		
F	7791500029 // CABLE 1MM L.H. H05Z1-K BLACK									
	Wire number	Origin	Destination	Reference	Wire description	Color code	Section	Length (mm)	Origen Lug	Destination Lug
	8	-P1:24V	-X2.1:1	7791500029	7791500029 // CABLE 1MM L.H. H05Z1-K BLACK	BK	1 (mm²)	280	9019070000 // Tubular lug	9019070000 // Tubular lug
	10	-P1:0V	-X3.1:1	7791500029	7791500029 // CABLE 1MM L.H. H05Z1-K BLACK	BK	1 (mm²)	278	9019070000 // Tubular lug	9019070000 // Tubular lug
	11	-P1:A	-X4.1:1	7791500029	7791500029 // CABLE 1MM L.H. H05Z1-K BLACK	BK	1 (mm²)	280	9019070000 // Tubular lug	9019070000 // Tubular lug
	12	-P1:B	-X5.1:1	7791500029	7791500029 // CABLE 1MM L.H. H05Z1-K BLACK	BK	1 (mm²)	280	9019070000 // Tubular lug	9019070000 // Tubular lug
	27	-P3:+	-X2.1:3	7791500029	7791500029 // CABLE 1MM L.H. H05Z1-K BLACK	BK	1 (mm²)	189	9019070000 // Tubular lug	9019070000 // Tubular lug
	28	-P3:-	-X3.1:3	7791500029	7791500029 // CABLE 1MM L.H. H05Z1-K BLACK	BK	1 (mm²)	191	9019070000 // Tubular lug	9019070000 // Tubular lug
	29	-P3:B	-X5.1:3	7791500029	7791500029 // CABLE 1MM L.H. H05Z1-K BLACK	BK	1 (mm²)	193	9019070000 // Tubular lug	9019070000 // Tubular lug
	30	-P3:A	-X4.1:3	7791500029	7791500029 // CABLE 1MM L.H. H05Z1-K BLACK	BK	1 (mm²)	195	9019070000 // Tubular lug	9019070000 // Tubular lug
	51	-P2:+	-X2.1:4	7791500029	7791500029 // CABLE 1MM L.H. H05Z1-K BLACK	BK	1 (mm²)	348	9019070000 // Tubular lug	9019070000 // Tubular lug
	52	-P2:-	-X3.1:4	7791500029	7791500029 // CABLE 1MM L.H. H05Z1-K BLACK	BK	1 (mm²)	353	9019070000 // Tubular lug	9019070000 // Tubular lug
	53	-P2:B	-X5.1:4	7791500029	7791500029 // CABLE 1MM L.H. H05Z1-K BLACK	BK	1 (mm²)	365	9019070000 // Tubular lug	9019070000 // Tubular lug
E	54	-P2:A	-X4.1:4	7791500029	7791500029 // CABLE 1MM L.H. H05Z1-K BLACK	BK	1 (mm²)	360	9019070000 // Tubular lug	9019070000 // Tubular lug
								3312		
	7791500030 // CABLE 1MM L.H. H05Z1-K RED									
	Wire number	Origin	Destination	Reference	Wire description	Color code	Section	Length (mm)	Origen Lug	Destination Lug
	1	-P1:IN1+	-K1:2	7791500030	7791500030 // CABLE 1MM L.H. H05Z1-K RED	RD	1 (mm²)	677	9019070000 // Tubular lug	9200640000 // Faston lug
	2	-P1:IN1-	-K1:1	7791500030	7791500030 // CABLE 1MM L.H. H05Z1-K RED	RD	1 (mm²)	691	9019070000 // Tubular lug	9200640000 // Faston lug
	3	-P1:IN2-	-F91.COM:11	7791500030	7791500030 // CABLE 1MM L.H. H05Z1-K RED	RD	1 (mm²)	655	9019070000 // Tubular lug	9019070000 // Tubular lug
	5	-P1:IN2+	-F91.COM:14	7791500030	7791500030 // CABLE 1MM L.H. H05Z1-K RED	RD	1 (mm²)	651	9019070000 // Tubular lug	9019070000 // Tubular lug
								2674		
	7791500325 // CABLE 1X4MM^2 PV H1Z2Z2-K BLACK									
	Wire number	Origin	Destination	Reference	Wire description	Color code	Section	Length (mm)	Origen Lug	Destination Lug
	4	-P1:PV-	-X73.1:8	7791500325	7791500325 // CABLE 1X4MM^2 PV H1Z2Z2-K BLACK	BK	4 (mm²)	933	9004110000 // Tubular lug (without insulation)	4000001964 // M8 Ring lug
								933		
B										
	A									

Additional product documents				1.				Tolerances: ISO 2768-mK		
				2.						
					Date	Name	Weidmüller			
				Drawn	08/06/2023	wm01276				
				Checked			Description: PV 220S0F3CXXV0O0TA1PA15LWM			
				Criterion for print						
				1 : 1		A3	Drawing-No / Material-No: 8000119550			
				Customer:						
				WEIDMÜLLER, S.A.			drw Index 0		Sheet 3 / 5	
0			08/06/2023	wm01276	Customer-No: 104000066					
Index	Brief Description			Date	Name	Customer Description:				

8	7	6	5	4	3	2	1
---	---	---	---	---	---	---	---

Additional product documents				1.				Tolerances: ISO 2768-mK					
				2.									
					Date	Name							
				Drawn	08/06/2023	wm01276							
				Checked									
				Criterion for print				Description:					
				1 : 1	A3		PV 220S0F3CXXV0O0TA1PA15LWW						
				Customer:				Drawing-No / Material-No: 8000119550					
				WEIDMÜLLER, S.A.									
				Customer-No:				03/5					
0				08/06/2023	wm01276		104000066						
Index	Brief Description			Date	Name		Customer Description:						

WEIERGABE SOME Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
ZUWIDERHANDLUNGEN VERFÜHREN ZU SCHADENSATZ. ALE RECHTE DER FÜR DEN FALL DER PATENT-, GEBRAUCHSMUSTER-, ODER GESCHMACKSMUSTERRECHTUNG VORBEHALTEN.
THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT AS WELL AS THE COMMUNICATION OF ITS CONTENTS TO OTHERS WITHOUT EXPLICIT AUTHORIZATION IS PROHIBITED.
WEIDMÜLLER reserves the right to file for patents, utility models or designs.
WEIDMÜLLER INTERFACE GmbH & Co. KG

8		7		6		5		4		3		2		1	
7791500345 // CABLE 1X4MM^2 PV H1Z2Z2-K RED															
F	Wire number	Origin	Destination	Reference	Wire description		Color code	Section	Length (mm)	Origen Lug		Destination Lug			
	41	-P1:PV+	-X71.1:23	7791500345	7791500345 // CABLE 1X4MM^2 PV H1Z2Z2-K RED		RD	4 (mm²)	715	9004110000 // Tubular lug (without insulation)		4000001964 // M8 Ring lug			
	43	-(+)F1:2	-X71.1:20	7791500345	7791500345 // CABLE 1X4MM^2 PV H1Z2Z2-K RED		RD	4 (mm²)	210	0373100000 // Tubular lug (without insulation)		4000001964 // M8 Ring lug			
	44	-(+)F2:2	-X71.1:19	7791500345	7791500345 // CABLE 1X4MM^2 PV H1Z2Z2-K RED		RD	4 (mm²)	202	0373100000 // Tubular lug (without insulation)		4000001964 // M8 Ring lug			
	45	-(+)F3:2	-X71.1:16	7791500345	7791500345 // CABLE 1X4MM^2 PV H1Z2Z2-K RED		RD	4 (mm²)	206	0373100000 // Tubular lug (without insulation)		4000001964 // M8 Ring lug			
	46	-(+)F4:2	-X71.1:15	7791500345	7791500345 // CABLE 1X4MM^2 PV H1Z2Z2-K RED		RD	4 (mm²)	202	0373100000 // Tubular lug (without insulation)		4000001964 // M8 Ring lug			
	47	-(+)F5:2	-X71.1:12	7791500345	7791500345 // CABLE 1X4MM^2 PV H1Z2Z2-K RED		RD	4 (mm²)	205	0373100000 // Tubular lug (without insulation)		4000001964 // M8 Ring lug			
	48	-(+)F6:2	-X71.1:11	7791500345	7791500345 // CABLE 1X4MM^2 PV H1Z2Z2-K RED		RD	4 (mm²)	205	0373100000 // Tubular lug (without insulation)		4000001964 // M8 Ring lug			
	49	-(+)F7:2	-X71.1:8	7791500345	7791500345 // CABLE 1X4MM^2 PV H1Z2Z2-K RED		RD	4 (mm²)	211	0373100000 // Tubular lug (without insulation)		4000001964 // M8 Ring lug			
	50	-(+)F8:2	-X71.1:7	7791500345	7791500345 // CABLE 1X4MM^2 PV H1Z2Z2-K RED		RD	4 (mm²)	212	0373100000 // Tubular lug (without insulation)		4000001964 // M8 Ring lug			
	55	-(+)F9:2	-X71.1:4	7791500345	7791500345 // CABLE 1X4MM^2 PV H1Z2Z2-K RED		RD	4 (mm²)	227	0373100000 // Tubular lug (without insulation)		4000001964 // M8 Ring lug			
	56	-(+)F10:2	-X71.1:3	7791500345	7791500345 // CABLE 1X4MM^2 PV H1Z2Z2-K RED		RD	4 (mm²)	239	0373100000 // Tubular lug (without insulation)		4000001964 // M8 Ring lug			
	57	-(+)F11:2	-X71.1:1	7791500345	7791500345 // CABLE 1X4MM^2 PV H1Z2Z2-K RED		RD	4 (mm²)	428	0373100000 // Tubular lug (without insulation)		4000001964 // M8 Ring lug			
	58	-(+)F12:2	-X71.1:2	7791500345	7791500345 // CABLE 1X4MM^2 PV H1Z2Z2-K RED		RD	4 (mm²)	427	0373100000 // Tubular lug (without insulation)		4000001964 // M8 Ring lug			
	59	-(+)F13:2	-X71.1:5	7791500345	7791500345 // CABLE 1X4MM^2 PV H1Z2Z2-K RED		RD	4 (mm²)	452	0373100000 // Tubular lug (without insulation)		4000001964 // M8 Ring lug			
	60	-(+)F14:2	-X71.1:6	7791500345	7791500345 // CABLE 1X4MM^2 PV H1Z2Z2-K RED		RD	4 (mm²)	466	0373100000 // Tubular lug (without insulation)		4000001964 // M8 Ring lug			
	61	-(+)F15:2	-X71.1:9	7791500345	7791500345 // CABLE 1X4MM^2 PV H1Z2Z2-K RED		RD	4 (mm²)	500	0373100000 // Tubular lug (without insulation)		4000001964 // M8 Ring lug			
62	-(+)F16:2	-X71.1:10	7791500345	7791500345 // CABLE 1X4MM^2 PV H1Z2Z2-K RED		RD	4 (mm²)	517	0373100000 // Tubular lug (without insulation)		4000001964 // M8 Ring lug				
63	-(+)F17:2	-X71.1:13	7791500345	7791500345 // CABLE 1X4MM^2 PV H1Z2Z2-K RED		RD	4 (mm²)	557	0373100000 // Tubular lug (without insulation)		4000001964 // M8 Ring lug				

Additional product documents				1.					Tolerances: ISO 2768-mK						
				2.											
						Date	Name								
						Drawn	08/06/2023	wm01276							
						Checked			Description:						
						Criterion for print									
						1 : 1	A3	PV 220S0F3CXXV0O0TA1PA15LWW							
						Customer:		Drawing-No / Material-No:							
						WEIDMÜLLER, S.A.									
						Customer-No:		8000119550		drw Index	Sheet				
0				08/06/2023	wm01276	104000066									
Index	Brief Description			Date	Name	Customer Description:									

WEIDMÜLLER INTERFACCE GmbH & Co. KG
WEIDMÜLLER SYSTEM RESERVES THE RIGHT TO FILE FOR PATENTS, UTILITY MODELS OR DESIGNS.
OFFENDERS WILL BE HELD LIABLE FOR THE PAYMENT OF DAMAGES.
ZUWIDERHANDLUNGEN VERPFLICHTEN ZU SCHADENSERSATZ. ALLE RECHTE RUHEN FÜR DEN FALL DER PATENT-, GEBRAUCHSMUSTER-, ODER GESCHMACKSMUSTERENTRAGUNG VORBEHALTEN.
THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT AS WELL AS THE COMMUNICATION OF ITS CONTENTS TO OTHERS WITHOUT EXPLICIT AUTHORIZATION IS PROHIBITED.
WIEDERGABE SOMIT VERPFLICHTUNG DIESES DOKUMENTS, VERWERTUNG SEINES INHALTS SIND VERBOTEN, SOWEIT NICHT AUSDRUECKLICH GESTATET.
ZUWIDERHANDLUNGEN VERPFLICHTEN ZU SCHADENSERSATZ. ALLE RECHTE RUHEN FÜR DEN FALL DER PATENT-, GEBRAUCHSMUSTER-, ODER GESCHMACKSMUSTERENTRAGUNG VORBEHALTEN.
THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT AS WELL AS THE COMMUNICATION OF ITS CONTENTS TO OTHERS WITHOUT EXPLICIT AUTHORIZATION IS PROHIBITED.

	8	7	6	5	4	3	2	1		
F	-> 7791500345 // CABLE 1X4MM^2 PV H1Z2Z2-K RED									
	Wire number	Origin	Destination	Reference	Wire description	Color code	Section	Length (mm)	Origen Lug	Destination Lug
	64	-(+)F18:2	-X71.1:14	7791500345	7791500345 // CABLE 1X4MM^2 PV H1Z2Z2-K RED	RD	4 (mm²)	575	0373100000 // Tubular lug (without insulation)	4000001964 // M8 Ring lug
	65	-(+)F19:2	-X71.1:17	7791500345	7791500345 // CABLE 1X4MM^2 PV H1Z2Z2-K RED	RD	4 (mm²)	624	0373100000 // Tubular lug (without insulation)	4000001964 // M8 Ring lug
E	66	-(+)F20:2	-X71.1:18	7791500345	7791500345 // CABLE 1X4MM^2 PV H1Z2Z2-K RED	RD	4 (mm²)	637	0373100000 // Tubular lug (without insulation)	4000001964 // M8 Ring lug
								8017		
	7791500395 // CABLE 1X10MM^2 PV H1Z2Z2-K BLACK									
	Wire number	Origin	Destination	Reference	Wire description	Color code	Section	Length (mm)	Origen Lug	Destination Lug
D	13	-X41.Output:O	-X73.1:1	7791500395	7791500395 // CABLE 1X10MM^2 PV H1Z2Z2-K BLACK	BK	10 (mm²)	613	9019240000 // Tubular lug	7791300145 // M8 Ring lug
	23	-X42.Output:O	-X73.1:2	7791500395	7791500395 // CABLE 1X10MM^2 PV H1Z2Z2-K BLACK	BK	10 (mm²)	694	9019240000 // Tubular lug	7791300145 // M8 Ring lug
	31	-X43.Output:O	-X73.1:3	7791500395	7791500395 // CABLE 1X10MM^2 PV H1Z2Z2-K BLACK	BK	10 (mm²)	749	9019240000 // Tubular lug	7791300145 // M8 Ring lug
	32	-X44.Output:O	-X73.1:4	7791500395	7791500395 // CABLE 1X10MM^2 PV H1Z2Z2-K BLACK	BK	10 (mm²)	836	9019240000 // Tubular lug	7791300145 // M8 Ring lug
C	40	-X45.Output:O	-X73.1:5	7791500395	7791500395 // CABLE 1X10MM^2 PV H1Z2Z2-K BLACK	BK	10 (mm²)	808	9019240000 // Tubular lug	7791300145 // M8 Ring lug
								3700		
	7791500397 // CABLE 1X16MM^2 PV H1Z2Z2-K BLACK									
	Wire number	Origin	Destination	Reference	Wire description	Color code	Section	Length (mm)	Origen Lug	Destination Lug
B	7	-F91.+:+ -	-X73.1:7	7791500397	7791500397 // CABLE 1X16MM^2 PV H1Z2Z2-K BLACK	BK	16 (mm²)	605	9019260000 // Tubular lug	7791300146 // M8 Ring lug
								605		
	7791500398 // CABLE 1X16MM^2 PV H1Z2Z2-K RED									
	Wire number	Origin	Destination	Reference	Wire description	Color code	Section	Length (mm)	Origen Lug	Destination Lug
A	42	-F91.-:-+	-X71.1:24	7791500398	7791500398 // CABLE 1X16MM^2 PV H1Z2Z2-K RED	RD	16 (mm²)	634	9019260000 // Tubular lug	7791300146 // M8 Ring lug
								634		
	Additional product documents									
	1.								Tolerances: ISO 2768-mK	
2.										
					Date	Name				
					Drawn	08/06/2023				wm01276
					Checked					
					Criterion for print		Description:			
					1 : 1	A3	PV 220S0F3CXXV0O0TA1PA15LWW			
					Customer:		Drawing-No / Material-No:			
					WEIDMÜLLER, S.A.		8000119550			
					Customer-No:		drw Index	Sheet		
0					08/06/2023	wm01276	0	5/5		
Index	Brief Description				Date	Name	Customer Description:			