


The reproduction, distribution and utilization of this document as well as the communication of its contents to others without explicit authorization is prohibited. Offenders will be held liable for the payment of damages. Weidmueller exclusively reserves the right to file for patents, utility models or designs.

© Weidmüller Interface GmbH & Co. KG



For the mounting of PCBs, it should be noted that the rated data relates only to the PCB components alone. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to IEC 664 / VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine

Weidmüller PCB components are tested to the DIN EN 61984 standard, and are valid for its field of application. Provided that the components are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

 DIN ISO 2768-m				Cat.no.:
	95845/0 24.05.18 AMANN_A	02	<b>Weidmüller</b> 	3 19703 14
	Modification		Drawing no.	Issue no.
	Date	Name	Sheet 02 of 03 sheets	
	Drawn	21.11.2007	HELIS_MA	
	Responsible		AMANN_A	
Scale: 2/1	Checked	25.05.2018	HELIS_MA	
Supersedes: .	Approved	LANG_T	Product file: SLDF 5.08	7306

# SLDF 5.08 L/F..

STIFTLEISTE  
PIN HEADER

7306