




Fehl. Masse und Angaben siehe Datenblatt
Further dim. & info. see data sheet

For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller connectors are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the connectors are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.



P = 7.62 Raster
Pitch

D = 01.3
0.51"

d = 1.2
0.047"

n = Polzahl/ number of poles

shown: SL 7.62HP/05/180F
General tolerance:
DIN ISO 2768-mK

103327/5
03.04.18 HELIS_MA 00
RoHS
COMPLIANT


Modification

Drawn 28.06.2017 HELIS_MA

Responsible KRUG_M

Scale: 2:1 Checked 23.04.2018 HELIS_MA

Supersedes: . Approved LANG_T



4,5	+0.1 -0.3
3,2	+0.1 -0.3
MASS I / DIM I	TOLERANZ/ TOLERANCES
n L1 [mm]	L1 [inch]

12	83,82	3,300
11	76,20	3,000
10	68,58	2,700
9	60,96	2,400
8	53,34	2,100
7	45,72	1,800
6	38,10	1,500
5	30,48	1,200
4	22,86	0,900
3	15,24	0,600
2	7,62	0,300
n	L1 [mm]	L1 [inch]

Cat. no.:

3 4781 06

Drawing no.:

Sheet 02 of 03 sheets

Weidmüller

SL 7.62HP/..180...
STIFTLEISTE
MALE HEADER