



[1]

UNITED KINGDOM CONFORMITY ASSESSMENT  
**TYPE EXAMINATION CERTIFICATE**

[2] **Product or Protective System Intended for use in Potentially Explosive Atmospheres  
UKSI 2016:1107 (as amended by UKSI 2019:696)**

[3] Type Examination Certificate No.: **UL24UKEX2973X Rev. 1**

[4] Product: **Industrial Ethernet Switch, Model Series IE-SW-BLB**

[5] Manufacturer: **Weidmüller Interface GmbH & Co. KG**

[6] Address: **Klingenbergsstrasse 26, 32758 Detmold Germany**

[7] This product and any acceptable variation thereto are specified in the schedule to this certificate and the documents therein referred to.

[8] UL International (UK) Ltd certifies that this product has been found to comply with the Essential Health and Safety Requirements relating to the design and construction of products intended for use in potentially explosive atmospheres given in Schedule 1 of the Regulations. The examination and test results are recorded in the confidential report **UKRCC-BL-4791688381.1**.

[9] Compliance with the Essential Health and Safety Requirements has been assured by compliance with:

**EN IEC 60079-0:2018**      **EN 60079-7:2015**      **EN IEC 60079-7:2015/A1:2018**  
**EN IEC 60079-15:2019**

Except in respect of those requirements listed at section 19 of the schedule to this certificate.

[10] If the sign "X" is placed after the certificate number, it indicates that the product is subject to the Specific Conditions of Use specified in the Schedule to this certificate.

[11] This TYPE EXAMINATION CERTIFICATE relates only to the design and construction of the specified product. Further requirements of the Regulations apply to the manufacturing process and supply of this product. These are not covered by this certificate.

[12] The marking of the product shall include the following:

II 3 G    Ex ec IIC T4 Gc

II 3 G    Ex ec nC IIC T4 Gc

**Certification Officer**  
Andrew Moffat

This is to certify that the sample(s) of the Product described herein ("Certified Product") has been investigated and found in compliance with the Standard(s) indicated on this Certificate, in accordance with the UKEx Product Certification Program Requirements. This certificate and test results obtained apply only to the product sample(s) submitted by the Manufacturer. UL did not select the sample(s) or determine whether the sample(s) provided were representative of other manufactured product. UL has not established Follow-Up Service or other surveillance of the product. The Manufacturer is solely and fully responsible for conformity of all product to all applicable Standards, specifications, requirements or Directives. The test results may not be used, in whole or in part, in any other document without UL's prior written approval.

**Date of issue:** 2024-06-28

**Re-issued:** 2025-05-27

UL International (UK) Ltd Unit 1-3 Horizon Kingsland Business Park Wade Road, Basingstoke RG24 8AH, UK  
Phone : +44 (0)1256 312100

[13]

[14]

**Schedule**  
**TYPE EXAMINATION CERTIFICATE No.**  
**UL24UKEX2973X Rev. 1**

[15]

Description of Product

Industrial Ethernet Switch Model IE-SW-BLB Series have LAN ports and SFP slots with different amount and combination. These devices are evaluated as open-type devices, microcomputer based and communicate via interfaces through wire. They are intended for installation into a tool-accessible only ultimate enclosure and can be installed by DIN-Rail vertical mounting.

Models covered:

IE-SW-BLB-10-8GT-2GESFP;  
IE-SW-BLB-05-5GT and IE-SW-BLB-05-5GT-C;  
IE-SW-BLB-05-5TX and IE-SW-BLB-05-4TX-1FESFP;  
IE-SW-BLB-05-4GT-1GESFP  
IE-SW-BLB-08-6TX-2FESFP, IE-SW-BLB-08-7TX-1FESFP and IE-SW-BLB-08-8TX;  
IE-SW-BLB-08-8GT, IE-SW-BLB-08-8GT-C  
IE-SW-BLB-16-16TX, IE-SW-BLB-18-16TX-2GESFP and IE-SW-BLB-24-24TX.  
IE-SW-BLB-16-16GT, IE-SW-BLB-16-16GT-C and IE-SW-BLB-16-14GT-2GESFP

Nomenclature:

IE-SW-BLB	-	05	-	4TX	-	1FESFP	-	C
I		II		III		IV		V

I- Basic type designation:

IE-SW-BLB: Type designation

II- Total IO port number:

May be 05, 08, 10, 16, 18 or 24.

III- LAN port number and type:

GT: 10/100/1000Base-T(X) LAN port.  
TX: 10/100Base-T(X) LAN port.

IV- SFP connector number and type:

Blank: No SFP connector provided.

GESFP: 100/1000Base-X SFP Connector (For Models IE-SW-BLB-18-16TX-2GESFP, IE-SW-BLB-10-8GT-2GESFP, IE-SW-BLB-16-14GT-2GESFP, IE-SW-BLB-05-4GT-1GESFP only)

FESFP: 100Base-X SFP Connector (For Models IE-SW-BLB-05-4TX-1FESFP, IE-SW-BLB-08-6TX-2FESFP and IE-SW-BLB-08-7TX-1FESFP only)

V- Conformal coating (For IE-SW-BLB-05-5GT, IE-SW-BLB-08-8GT, IE-SW-BLB-16-16GT Series only):

C: Conformal Coating provided.

Blank: No conformal coating provided.

Model Difference:

Models IE-SW-BLB-05-5GT and IE-SW-BLB-05-5GT-C are identical except conformal coating is provided on the PWB of Model IE-SW-BLB-05-5GT-C.

Models IE-SW-BLB-05-5TX and IE-SW-BLB-05-4TX-1FESFP are identical except for the amount of LAN ports and SFP slot does not provide on Model IE-SW-BLB-05-5TX, and the enclosure openings for output ports.

Models IE-SW-BLB-08-6TX-2FESFP, IE-SW-BLB-08-7TX-1FESFP and IE-SW-BLB-08-8TX are identical except for the amount of LAN ports and SFP slots, and the enclosure openings for output ports.

Model IE-SW-BLB-16-16TX and IE-SW-BLB-24-24TX utilized identical Main Board, but no I/O Board provided on Model IE-SW-BLB-16-16TX, also with smaller enclosure size.

Model IE-SW-BLB-18-16TX-2GESFP and IE-SW-BLB-24-24TX are identical except for the amount of LAN ports and SFP slots, and the enclosure openings for output ports.

The optical radiation output of the product with respect to explosion protection, according to Annex II clause 1.3.1 of the Directive 2014/34/EU is covered in this certificate based on Exceptions 1) and 3) to the scope of EN 60079-28:2015.

Models IE-SW-BLB-08-8GT and IE-SW-BLB-08-8GT-C are identical except conformal coating is provided on the PWB of Model IE-SW-BLB-08-8GT-C.

Models IE-SW-BLB-16-16GT and IE-SW-BLB-16-16GT-C are identical except conformal coating is provided on the PWB of Model IE-SW-BLB-16-16GT-C.

Models IE-SW-BLB-16-16GT and IE-SW-BLB-16-14GT-2GESFP utilized identical Main Board except for the amount of LAN ports. Additional SFP Board provided on Model IE-SW-BLB-16-14GT-2GESFP, which has bigger enclosure size due to SFP ports.



**Solutions**

A UKAS accredited certification body No. 4705

This certificate may only be reproduced in its entirety and without any change, schedule included

Form-ULID-006123.2 – Issue 5.1

Page 2 of 4

[13]

[14]

**Schedule**  
**TYPE EXAMINATION CERTIFICATE No.**  
**UL24UKEX2973X Rev. 1**

Temperature range:

The relation between ambient temperature and the assigned temperature class is as follows:

Ambient temperature range	Temperature class
-40°C to +75°C	T4

Electrical data

Model	Input Rating	Relay Output	Marking
IE-SW-BLB-10-8GT-2GESFP	Dual 12-48 Vdc or 24 Vac, Max. 7.06 W	N/A	⊗ II 3 G Ex ec IIC T4 Gc
IE-SW-BLB-05-5GT	Dual 12-48 Vdc or 24 Vac, Max. 2.5 W		
IE-SW-BLB-05-5GT-C			
IE-SW-BLB-05-5TX	Dual 12-48 Vdc or 24 Vac, Max. 1.1 W		
IE-SW-BLB-05-4TX-1FESFP	Dual 12-48 Vdc or 24 Vac, Max. 1.8 W		
IE-SW-BLB-08-6TX-2FESFP	Dual 12-48 Vdc or 24 Vac, Max. 3.1 W		
IE-SW-BLB-08-7TX-1FESFP	Dual 12-48 Vdc or 24 Vac, Max. 2.4 W		
IE-SW-BLB-08-8TX	Dual 12-48 Vdc or 24 Vac, Max. 1.8 W		
IE-SW-BLB-08-8GT	Dual 12-48 Vdc, 24 Vac, Max. 4 W		
IE-SW-BLB-08-8GT-C			
IE-SW-BLB-05-4GT-1GESFP	Dual 12-48 Vdc or 24 Vac, Max. 3 W	24VDC, 1A, Resistive	⊗ II 3 G Ex ec nC IIC T4 Gc
IE-SW-BLB-16-16TX	Dual 12-48 Vdc or 24 Vac, Max. 4.5 W		
IE-SW-BLB-18-16TX-2GESFP	Dual 12-48 Vdc or 24 Vac, Max. 8.4 W		
IE-SW-BLB-24-24TX	Dual 12-48 Vdc or 24 Vac, Max. 6 W		
IE-SW-BLB-16-16GT	Dual 12-48 Vdc, 24 Vac, Max. 11.5 W		
IE-SW-BLB-16-16GT-C			
IE-SW-BLB-16-14GT-2GESFP	Dual 12-48 Vdc, 24 Vac, Max. 13 W		

Routine tests:

N/A

[16]

Test Report No. (associated with this certificate issue)

The test report no. is provided under item no. [ 8 ] on page 1 of this Type Examination Certificate.

[17]

Specific conditions of use:

- The equipment shall only be used in an area of at least pollution degree 2, as defined in EN 60664-1.
- The equipment shall be mounted on Din-rail in vertical position and installed in an enclosure that provides a minimum ingress protection of IP54 in accordance with EN IEC 60079-0 and only accessible by use of a tool, see installation instructions before use.
- Transient protection shall be provided that is set at a level not exceeding 140% of the peak rated voltage value at the supply terminals to the equipment.
- The equipment shall keep minimum installation clearances as following to prevent from overheating:
  - Top and bottom: 51 mm (2.0 inch)
  - Side: 51 mm (2.0 inch)
  - Front: 64 mm (2.5 inch).
- The input terminal block shall be used with conductors of 12 – 24 AWG wire size (ISO Metric size 4 - 0.2 mm<sup>2</sup>).

[18]

Conditions of certification:

None

[19]

Essential Health and Safety Requirements (Regulations Schedule 1)

In addition to the Essential Health and Safety Requirements covered by the standards listed at item 9, all other requirements are demonstrated in the relevant reports.

Additional information

The trademark



will be used as the company identifier on the marking label.



**Solutions**

A UKAS accredited certification body No. 4705

This certificate may only be reproduced in its entirety and without any change, schedule included

Form-ULID-006123.2 – Issue 5.1

Page 3 of 4

[13]

[14]

**Schedule**  
**TYPE EXAMINATION CERTIFICATE No.**  
**UL24UKEX2973X Rev. 1**

[20]

Drawings and Documents

Title:	Drawing No.:	Rev. Level:	Date:
Model IE-SW-BLB-10-8GT-2GESFP - Installation Instruction	2978380000	00	2024-01
Models IE-SW-BLB-05-5GT, IE-SW-BLB-05-5GT-C - Installation Instruction	2978410000	00	2024-01
Models IE-SW-BLB-05-5TX, IE-SW-BLB-05-4TX-1FESFP -- Installation Instruction	2978400000	00	2024-05
Models IE-SW-BLB-08-8TX, IE-SW-BLB-08-7TX-1FESFP, IE-SW-BLB-08-6TX-2FESFP - Installation Instruction	2978390000	00	2024-05
Models IE-SW-BLB-16-16TX, IE-SW-BLB-18-16TX-2GESFP, IE-SW-BLB-24-24TX - Installation Instruction	2978420000	00	2024-05
Models IE-SW-BLB-08-8GT, IE-SW-BLB-08-8GT-C - Installation Instruction	3098210000	01	2024-11
Models IE-SW-BLB-16-16GT, IE-SW-BLB-16-16GT-C, IE-SW-BLB-16-14GT-2GESFP - Installation Instruction	3024080000	01	2024-11
Models IE-SW-BLB-05-4GT-1GESFP - Installation Instruction	3024070000	01	2024-11
Model IE-SW-BLB-10-8GT-2GESFP – Marking Label	2978380000-Label	00	2024-01
Models IE-SW-BLB-05-5GT and IE-SW-BLB-05-5GT-C – Marking Label	2978410000-Label	00	2024-01
Models IE-SW-BLB-05-5TX and IE-SW-BLB-05-4TX-1FESFP – Marking Label	2978400000-Label	00	2024-05
Models IE-SW-BLB-08-6TX-2FESFP, IE-SW-BLB-08-7TX-1FESFP and IE-SW-BLB-08-8TX – Marking Label	2978390000-Label	00	2024-05
Models IE-SW-BLB-16-16TX, IE-SW-BLB-18-16TX-2GESFP and IE-SW-BLB-24-24TX –Marking Label	2978420000-Label	00	2024-05
Models IE-SW-BLB-08-8GT, IE-SW-BLB-08-8GT-C - Marking Label	2908080000-Label 2908110000-Label	01	2024-11
Models IE-SW-BLB-16-16GT, IE-SW-BLB-16-16GT-C, IE-SW-BLB-16-14GT-2GESFP -Marking Label	2908090000-Label 2908120000-Label 2908130000-Label	01	2024-11
Models IE-SW-BLB-05-4GT-1GESFP - Marking Label	2908180000-Label	01	2024-11



**Solutions**

A UKAS accredited certification body No. 4705

This certificate may only be reproduced in its entirety and without any change, schedule included

Form-ULID-006123.2 – Issue 5.1

Page 4 of 4