





SHOWN: BLL7.62HP/05/180 3.2 SN



HOLE PATTERN



M 1:1

KUNDENZEICHNUNG
CUSTOMER DRAWING

12	83,82	3,30
11	76,20	3,00
10	68,58	2,70
9	60,96	2,40
8	53,34	2,10
7	45,72	1,80
6	38,10	1,50
5	30,48	1,20
4	22,86	0,90
3	15,24	0,60
2	7,62	0,30
n	L1 (mm)	L1 (inch)

3,2
4,5
pin length
1

For the mounting of PCBs, it should be noted that the rated data relates only to the PCB components alone.

The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to IEC 664 / VDE 0110.

The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller PCB components are tested to the DIN EN 61984 standard, and are valid for its field of application.

Provided that the components are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.



DIN ISO 2768-m

94360/4
11.05.17 HELIS_MA 00

Modification

Weidmüller

3 50817 05
Drawing no. Sheet 01 of 03 sheets
Issue no.

	Date	Name		Cat.no.: . . .
	Drawn	21.09.2009		
	Responsible	KRUG_M		
Scale: 2:1	Checked	08.06.2018	HELIS_MA	
Supersedes: .	Approved	08.06.2018	LANG_T	Product file: BLL7.62HP

BLL 7.62HP/..180...
BUCHSENLEISTE
SOCKET BLOCK

7373