

Document No. **UKCA PA53 210624 002 ISS 01**

Manufacturer **Weidmüller Interface GmbH & Co. KG**

Address **Klingenbergstr. 26
32758 Detmold, Germany**

Object of the declaration **VPU AC I Series**

☒ Continued on page 2

The manufacturer attests, in sole-responsibility, that the object of the declaration described above is in conformity with the essential requirements of directive(s):

		Directive
☒ The Electrical Equipment (Safety) Regulations 2016	SI 2016/1101	SI2019/696(Schedule23) SI 2020/1460
☐ The Electromagnetic Compatibility Regulations 2016	SI 2016/1091	SI2019/696(Schedule20) SI 2020/1460
☐ The supply of Machinery (Safety) Regulations 2008	SI 2008/1597	SI2019/696(Schedule12) SI 2020/1460
☐ The Radio Equipment Regulations 2017	SI 2017/1206	SI2019/696(Schedule29) SI 2020/1460
☒ The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012 RoHS	SI 2012/3032	SI2019/188
☐ The Equipment and Protective Systems Intended for Use in Potentially Explosive Atmospheres Regulations 2016 Marking (Equipment Group, Category, Atmosphere)	SI 2016/1107	SI2019/696(Schedule25) SI 2020/1460

References to the relevant EN or BSEN designated standards used, or references to the specifications, in relation to which conformity is declared:

EN 61643-11:2012

Document No. **UKCA PA53 210624 002 ISS 01**

2636900000	VPU AC I 0 300/12.5 LCF
2636910000	VPU AC I 3+1 300/12.5 LCF
2636920000	VPU AC I 3+1 R 300/12.5 LCF
2636930000	VPU AC I 1+1 300/12.5 LCF
2636940000	VPU AC I 1+1 R 300/12.5 LCF
2636950000	VPU AC I 1 300/12.5 LCF
2636960000	VPU AC I 1 R 300/12.5 LCF
2636970000	VPU AC I 3 300/12.5 LCF
2636980000	VPU AC I 3 R 300/12.5 LCF
2591370000	VPU AC I 0 300/12.5
2591380000	VPU AC I 1 300/12.5
2591390000	VPU AC I 1 R 300/12.5
2591400000	VPU AC I 2 300/12.5
2591410000	VPU AC I 2 R 300/12.5
2591420000	VPU AC I 4 300/12.5
2591430000	VPU AC I 4 R 300/12.5
2591440000	VPU AC I 3 300/12.5
2591450000	VPU AC I 3 R 300/12.5
2591460000	VPU AC I 3+1 300/12.5
2591470000	VPU AC I 3+1 R 300/12.5
2591480000	VPU AC I 1+1 300/12.5
2591490000	VPU AC I 1+1 R 300/12.5

2591500000	VPU AC I 0 480/10
2591510000	VPU AC I 1 480/10
2591520000	VPU AC I 1 R 480/10
2591530000	VPU AC I 3 480/10
2591540000	VPU AC I 3 R 480/10
2591550000	VPU AC I 4 480/10
2591560000	VPU AC I 4 R 480/10
2591570000	VPU AC I 1 N-PE 305/50
2591590000	VPU AC I 0 N-PE 305/50
2668450000	VPU AC I 0 N-PE 305/50 LCF
2619120000	VPU AC I 1 R 440/25 LCF
2619100000	VPU AC I 1 440/25 LCF
2619140000	VPU AC I 2 R 440/25 LCF
2619130000	VPU AC I 2 440/25 LCF
2619220000	VPU AC I 1+1 R 440/25 LCF
2619210000	VPU AC I 1+1 440/25 LCF
2619170000	VPU AC I 3 R 440/25 LCF
2619160000	VPU AC I 3 440/25 LCF
2619260000	VPU AC I 3+1 R 440/25 LCF
2619240000	VPU AC I 3+1 440/25 LCF
2619190000	VPU AC I 4 R 440/25 LCF
2619200000	VPU AC I 4 440/25 LCF

Detmold, 09.08.2021

place, date

legally binding signature

Thomas Peter Vice President Business Unit Digital Signaling & Protection

name and function

This declaration certifies compliance with the indicated directive but no warranty of properties. The safety instructions of the accompanying product documentation shall be observed.