







ALLGEMEINGUELTIGE KUNDENZEICHNUNG, AKTUELLER STAND NUR AUF ANFRAGE
GENERAL CUSTOMER DRAWING, TOPICAL VERSION ONLY IF REQUIRED



DETAIL A
X 5/1



M 1/1



P=3.50 RASTER
PITCH
D=Ø1.3 +0.1
d=0.5x0.8

For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance with VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller connectors are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the connectors are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

SHOWN : BLL 3.50/04/180

HOLE PATTERN

12	38.5	1.516	1	X	0	X	0	X	0	X	0	X	0	X	0	
			2	0	X	0	X	0	X	0	X	0	X	0	X	
11	35.0	1.378	1	X	0	X	0	X	0	X	0	X	0	X		
			2	0	X	0	X	0	X	0	X	0	X	0		
10	31.5	1.240	1	X	0	X	0	X	0	X	0	X	0			
			2	0	X	0	X	0	X	0	X	0	X			
9	28.0	1.102	1	X	0	X	0	X	0	X	0	X				
			2	0	X	0	X	0	X	0	X	0				
8	24.5	0.965	1	X	0	X	0	X	0	X	0					
			2	0	X	0	X	0	X	0	X					
7	21.0	0.827	1	X	0	X	0	X	0	X						
			2	0	X	0	X	0	X	0						
6	17.5	0.689	1	X	0	X	0	X	0							
			2	0	X	0	X	0	X							
5	14.0	0.551	1	X	0	X	0	X								
			2	0	X	0	X	0								
4	10.5	0.413	1	X	0	X	0									
			2	0	X	0	X									
3	7.0	0.276	1	X	0	X										
			2	0	X	0										
2	3.5	0.138	1	X	0											
			2	0	X											
n	POLZAHL POLES	L1 [mm]	L1 [inch]	REIHE/ ROW	1	2	3	4	5	6	7	8	9	10	11	12

GENERAL TOLERANCE:
DIN ISO 2768-m



80439/5
17.02.15 HELIS_MA 01

MODIFICATION



DATE NAME
DRAWN 22.04.2005 FROEHLKING_M

RESPONSIBLE LANG_T

CHECKED 17.02.2015 HELIS_MA

APPROVED LANG_T

SCALE: 2/1

SUPERSEDES: .

Weidmüller

BLL 3.50/.../180...
BUCHSENLEISTE
FEMALE HEADER

PRODUCT FILE: BLL 3.50

CAT.NO.: .

C 33133 14

DRAWING NO. ISSUE NO.
SHEET 01 OF 01 SHEETS

7369