

UK Attestation of Conformity

Document No. **UKCA DE PT1001 210819 002 ISSUE01**

Manufacturer **Weidmüller Interface GmbH & Co. KG**

Address **Klingenbergstr. 26
32758 Detmold, Germany**

Object of the declaration **WDK – Series / Double level terminal blocks**

☒ Continued on page 2

The manufacturer attests, in sole-responsibility, that the object of the declaration described above is in conformity with the essential requirements of directive(s):

	Directive	
The Equipment and Protective Systems Intended for Use in Potentially Explosive Atmospheres Regulations 2016 Marking (Equipment Group, Category, Atmosphere)	SI 2016/1107	SI2019/696(Schedule25) SI 2020/1460

References to the relevant BSEN or EN designated standards used, or references to the specifications, in relation to which conformity is declared:

EN IEC 60079-0:2018
EN IEC 60079-7:2015/A1:2018

Issued certificates from Approved Bodies

Approved Body (name, address and number)	Description of intervention	Certificate
ExVeritas, Units 16-18, Abenbury Way, Wrexham Industrial Estate, Wrexham, United Kingdom LL13 9UZ. Approved Body # 2585	Surveillance of production process (UKCA Ex)	ExVeritas 21UKQAN0176
Dekra Certification UK Ltd; Stokenchurch House, Oxford Road, Stokenchurch, HP14 3SX Approved Body # 8505	Surveillance of production process (UKCA Ex)	DEKRA 21UKQANxxxx
UL International (UK) Ltd Unit 1-3 Horizon Kingsland Business Park Wade Road, Basingstoke RG24 8AH, Approved Body # 0843	UKEx-Type Examination UKCA	UL21UKEX2116U

Detmold, 04.03.2022
Ort, Datum / place, date


Rechtsverbindliche Unterschrift / legally binding signature

Name und Funktion / name and function

Arnd Schepmann, Business Unit Leiter Terminals

This declaration certifies compliance with the indicated directive but no warranty of properties. The safety instructions of the accompanying product documentation shall be observe.

UK Attestation of Conformity

Document No.

UKCA DE PT1001 210819 002 ISSUE01

Object of the declaration

WDK 2.5N	1041600000
WDK 2.5N BL	1041680000
WDK 2.5N DU-PE	1041650000
WDK 2.5N PE	1041620000
WDK 2.5N V	1041610000
WDK 2.5 ZQV	1041100000
WDK 2.5 ZQV BL	1041180000
WDK 2.5 ZQV BR	1067950000
WDK 2.5 ZQV GE	1068040000
WDK 2.5 ZQV GN	1067960000
WDK 2.5 ZQV GR	1067970000
WDK 2.5 ZQV OR	1067990000
WDK 2.5 ZQV RT	1068010000
WDK 2.5 ZQV SW	1067940000
WDK 2.5 ZQV VI	1068020000
WDK 2.5 ZQV WS	1068030000
WDU 2,5/EX	1029100000
WDK 2.5PE	1036300000
WDK 2.5 DU-PE	1036400000
WDK 2.5V	1022300000
WDK 2.5V BL	1022380000
WDK 2.5V GE	1022350000
WDK 2.5V OR	1022360000
WDK 2.5	1021500000
WDK 2.5 BL	1021580000
WDK 2.5 OR	1021560000
WDK 4N PE	1041920000
WDK 4N	1041900000
WDK 4N BL	1041980000
WDK 4N BR	1068060000
WDK 4N GE	1068110000
WDK 4N GN	1073320000
WDK 4N GR	1068070000
WDK 4N GR 7042	1859020000
WDK 4N OR	1041960000
WDK 4N RT	1068080000
WDK 4N SW	1068050000
WDK 4N VI	1068090000
WDK 4N WS	1068100000
WDK 4N DU-PE	1041950000

UK Attestation of Conformity

WDK 4N V	1041910000
WDK 4N V BL	1111730000

WDK 1.5/R3.5	1753290000
WDK 1.5/R3.5 BL	1754180000

WDK 2.5V ZQV	2739600000
WDK 2.5V ZQV BL	2739610000
WDK 2.5V ZQV OR	2732600000