

## IOT-GW30 devices



**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

ID	Typ	SW Vers.
GW	IOT-GW30	V2.4.0
GWEU	IOT-GW30-4G-EU	
GWNA	IOT-GW30-4G-NA	
IBOX	FP IOT MD01 LAN S2 00000 see ID "GW"	
IBOXEU	FP IOT MD01 4EU S2 00000 see ID „GWEU“	

## u-OS products

This Security Data Sheet provides you with a condensed overview of the security functions of the devices (basic u-OS functionality without extinctions). It is an addition to the product specific documentation (see Weidmüller Support Center)

- Online documentation u-OS – IOT-GW30
- Quick references / quick start guide

**IOT-GW30 devices**

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Security intended use:**

The products of the IOT-GW30 series are designed for collecting, preprocessing, storing, and forwarding data from sensor-actuator systems or controllers via bus systems in industrial applications. The product can be connected to higher-level computer networks via Ethernet and communicate with the Internet via mobile communications. Communication via Ethernet or other bus systems is assumed to be secure; i.e. the customer is responsible for preventing unauthorized access to their devices, systems, machines, and networks by means of access restrictions (e.g., access control, locked control cabinet). Networks with different security levels should only be connected with appropriate security measures, such as routers with firewalls. Communication via the Internet using mobile communications should only take place using secure communication (e.g., VPN or TLS).

The IOT-GW30 products are based on the Weidmüller Linux based operating system u-OS. Individual applications are implemented using installable apps (from the Weidmüller App Hub) or directly installable Docker containers. Operation is web-based and is carried out using a browser. Special security measures must be implemented, which are described in detail in supplementary documentation. See chapter "General information".

The device is not intended for storing or processing personal data or for carrying out financial transactions.

Weidmüller recommends a security risk analysis for the specific application and the use of an information security management system to manage all infrastructural, organizational, and personnel measures necessary to maintain information security.

The IOT-GW30 products comply with protection class IP20 (according to IEC 60529). Proper use also includes observing the documentation supplied. The products may only be used for the intended applications.

If the products are used in a manner other than that intended by the manufacturer, the protective function they provide may be impaired. All work must only be carried out by trained specialists who are familiar with the applicable regulations and standards for the area of application.

**Note**

Only for IOT-GW30-4G-EU and IOT-GW30-4G-NA:

Observe the country-specific radio approvals. Check whether the device has radio approval for your location.

**License terms**

Components of free software are integrated into the IOT-GW30 products. The license terms can be accessed in u-OS. Observe the license terms.

## IOT-GW30 devices

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## General information

### Additional Security Documents

Comment	Reference
Weidmüller Industrial Security website with extensive information on legal requirements (e.g., RED-DA, Machinery Directive, Cyber Resilience Act, NIS2) and solutions with Weidmüller components and security services.	<a href="https://www.weidmueller.com/int/solutions/solutions/industrial_security/index.jsp">https://www.weidmueller.com/int/solutions/solutions/industrial_security/index.jsp</a>
The Weidmüller "Industrial Product Security Guideline" recommends security measures at the system level.	<a href="https://www.weidmueller.com/int/solutions/solutions/industrial_security/index.jsp">https://www.weidmueller.com/int/solutions/solutions/industrial_security/index.jsp</a>

### Weidmüller PSIRT (Product Security Response Team)

Comment	Link
Weidmueller has established a PSIRT and provides information on product-specific security vulnerabilities and their elimination on the Weidmüller website "Security Advisory Board"	<a href="https://support.weidmueller.com/support-center/popular-resources/security-advisory-board">https://support.weidmueller.com/support-center/popular-resources/security-advisory-board</a>
Weidmueller publishes security vulnerabilities of its products at VDE @CERT.	<a href="https://cert.vde.com/en/">https://cert.vde.com/en/</a>

### Weidmüller security activities

Weidmüller has implemented a certified Secure Product Development Process according to IEC62443-4-1.

Weidmüller will offer "Secure by Design" products in accordance with IEC62443-4-2. If required, please contact our sales staff

### Additional Support Center information

Headline	Comment	Reference
General	Further product-specific information and help can be found in the Weidmüller Support Center. Use the product type (e.g. IOT-GW30) in the search field.	<a href="https://support.weidmueller.com/support-center/">https://support.weidmueller.com/support-center/</a>

## IOT-GW30 devices

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## General information

### How to find product information

Device type **Physical/optic:** Type plate on device, Label on packaging  
**u-OS Welcome Screen** : Device information/ Product name  
**u-OS Data Hub:** u\_os\_adm/ manufacturer\_product\_type

Software version **u-OS Welcome Screen** : Device information/ u-OS version  
**u-OS Data Hub:** u\_os\_adm/ software\_version

Hardware version **Physical/optic:** Type plate on device, Label on packaging  
**u-OS Data Hub:** u\_os\_adm/ hardware\_version

MAC address **Physical/optic:** Type plate on device

Serial number **Physical/optic:** Type plate on device, Label on packaging  
**u-OS Welcome Screen** : Device information/ Serial number  
**u-OS Data Hub:** u\_os\_adm/ serial\_number

Supported browsers Mozilla Firefox 102 or higher  
Google Chrome 114 or higher  
Microsoft Edge 115 or higher

App software version **u-OS Control Center:** Apps/ App manager

## IOT-GW30 devices

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## General information

### Additional Security Documents

Comment	Reference
The Weidmüller "Industrial Product Security Guideline" recommends security measures at the system level.	<a href="https://www.weidmueller.com/int/solutions/solutions/industrial_security/index.jsp">https://www.weidmueller.com/int/solutions/solutions/industrial_security/index.jsp</a>

### Weidmüller PSIRT (Product Security Response Team)

Comment	Link
Weidmueller has established a PSIRT and provides information on product-specific security vulnerabilities and their elimination on the Weidmüller website "Security Advisory Board"	<a href="https://support.weidmueller.com/support-center/popular-resources/security-advisory-board">https://support.weidmueller.com/support-center/popular-resources/security-advisory-board</a>
Weidmueller publishes security vulnerabilities of its products at VDE @CERT.	<a href="https://cert.vde.com/en/">https://cert.vde.com/en/</a>

### Weidmüller security activities

Weidmüller has implemented a certified Secure Product Development Process according to IEC62443-4-1.

Weidmüller will offer "Secure by Design" products in accordance with IEC62443-4-2. If required, please contact our sales contact

### Additional Support Center information

Headline	Comment	Reference
General	Further product-specific information and help can be found in the Weidmüller Support Center. Use the product type (e.g. IOT-GW30) in the search field.	<a href="https://support.weidmueller.com/support-center/">https://support.weidmueller.com/support-center/</a>

## IOT-GW30 devices

Weidmüller Interface GmbH & Co. KG  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Technical information

## Interfaces

Type	No	Default	Can be changed	Comment
<b>Ethernet</b> GW, GWEU, GWNA	2	Active	Yes	Disable unused interfaces. To disable interfaces see „Disabling ethernet interfaces“.
<b>RS485</b> GW, GWEU, GWNA	1	Active	No	Active, but not connected with a functionality. It can only be used by a specific application.
<b>RS232</b> GW, GWEU, GWNA	1	Active	No	Active, but not connected with a functionality. It can only be used by a specific application.
<b>CAN</b> GW, GWEU, GWNA	1	Active	No	Active, but not connected with a functionality. It can only be used by a specific application.
<b>USB</b> GW, GWEU, GWNA	1 (host)	Active	No	
<b>Radio 2G, 3G, 4G</b> GWEU, GWNA	1	Active	Yes, via SIM card	No active access from outside. A connection can only be established from the device.
<b>Digital Input</b> GW, GWEU, GWNA	2	Active	No	Active, but not connected with a functionality. It can only be used by a specific application.
<b>Digital Output</b> GW, GWEU, GWNA	1	Active	No	Active, but not connected with a functionality. It can only be used by a specific application.

## Network access functions

Function	Default	Can be changed	Comment
DHCP Client	Deactive	Yes	Static IP configuration is recommended.
Network load limiter	Active	No	Rate limiting for prevention of DoS attacks.
<b>Firewall for mobile radio</b> GWEU, GWNA, IBOXEU	Active	No	The firewall prevents active access from outside via mobile radio (3G/4G/LTE).
NTP Client	Active	Yes	A valid time is important for e.g. certificate verification. Choose a valid NTP server.

## IOT-GW30 devices

Weidmüller Interface GmbH & Co. KG  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Technical information

## Component access functions

Function	Default	Can be changed	Comment
Login & password	Active	Yes	<p>Default credentials: No.  When starting for the first time, the user must enter a user name and password. The first user is automatically logged in as admin. Minimum password length is 6 character.</p> <p>Strongly recommended to change to a strong and individual password!  Password policy: Minimum password length is 6 character.</p> <p>Note: Extended functionality is planned for future versions</p>
Identity & access	Active	Yes	<p>Identity and access management (Users &amp; Roles) can be configured in the u-OS Control Center -&gt; Identity &amp; access. Multiple Users and Roles can be configured. Different permissions can be assigned to Roles.</p> <p>Clients can be created for using APIs e.g. u-OS Data Hub. OAuth 2.0 client credentials flow is used (Identity &amp; access -&gt; Clients).</p> <p>Unauthorized access can be configured for APIs e.g. u-OS Data Hub or Apps (Identity &amp; access -&gt; Access -&gt; Unauthenticated access). This is not recommended in production.</p> <p>Note: Extended functionality is planned for future versions</p>
HTTPS	Active	Yes	Secure web access. Recommended for web access.
HTTP	Deactive	Yes	Not secure web access. Not recommended, disable function.
SSH	Deactive	Yes	SSH access. Not recommended in production.

## Software and Data

Function	Default	Can be changed	Comment
Backup & restore	On demand		Local Backup & Restore of Apps, data and settings via web browser is supported. The Backup is encrypted.
Firmware update	On demand		<p>Firmware updates, APP offline installations and other SWUs are signed. Signature is checked in installation process.</p> <p>Local firmware update via Web browser is supported (Welcome screen / u-OS control center / Software &amp; updates / Update &amp; installation).</p> <p>Remote firmware update be performed via hawkBit. For hawkBit configuration navigate to Welcome screen / u-OS Control Center / Software &amp; updates / hawkBit</p>
Logging	Yes	no	u-OS system log can be opened in the u-OS Control Center. The log is not persistent.

## IOT-GW30 devices

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Technical information

### Software and Data

Function	Default	Can be changed	Comment
App and service installation	On demand		<p>The u-OS operating system allows the system to be individually expanded using Apps, Docker containers or native services.</p> <p>Best security practices</p> <ul style="list-style-type: none"><li>• Make sure that you only download updates from trustworthy sources (e.g. Weidmüller APPHUB or Weidmüller Support Center)</li><li>• Check cyclically for new updates for the devices you are using.</li><li>• Install software updates and security fixes as quickly as possible.</li><li>• Bring the machine or system into a safe state before the update.</li><li>• Test the new software before installing it on a large scale.</li><li>• Make sure that service personnel are present at the machine or system during an automatic update so that they can react in the event of a security incident.</li><li>• Create and update your security risk analysis.</li></ul>

## IOT-GW30 devices

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Technical information

### Services and Ports

**Note:**

- Additional ports may be available through installed Apps, Docker containers or services.

Function	Port	Protocol	Default	Can be changed	Comment
<b>HTTP</b> all	80	TCP	Deactive	Yes	Web access unsecure
<b>HTTPS</b> all	443	TCP	Active	Yes	Web access secure
<b>SSH</b> all	22	TCP	Deactive	Yes	Secure Shell Protocol
<b>Codemeter</b> all	22350	TCP	Active	No	Licence management
<b>LLMNR</b> all	5355	TCP/UDP	Active	No	Link-Local Multicast Name Resolution
<b>mDNS</b> all	5353	UDP	Active	No	Multicast DNS
<b>avahi-daemon</b>	Dynamic (32768 - 61000)	UDP	Active	No	Multicast DNS Queries
<b>SFTP</b>	22	SSH	Deactive	Yes	SSH File Transfer Protocol
<b>TLS versions supported</b>					Supported version 1.2 and 1.3

## IOT-GW30 devices

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

### Disabling ethernet interfaces

**Note:**

- Disabling of interfaces should only be performed by trained personnel and administrators.

Before disabling or enabling an interface, the following conditions must be met:

- SSH access must be enabled.
- An administrator must be connected to the device terminal.

Explanation

- Auto-connect: Prevents an interface from automatically establishing a connection when a cable is plugged in.
- Disconnect: Terminates the current active connection of the interface.

### Disabling an interface

Disable auto-connect:

- “nmcli connection modify “<eth0|eth1>” connection.autoconnect no”

Disconnect the interface:

- “nmcli device disconnect <eth0|eth1>”

### Enabling an interface

Enable auto-connect:

- “nmcli connection modify “<eth0|eth1>” connection.autoconnect yes”

Connect the interface:

- “nmcli device connect <eth0|eth1>”

**Important:** Always ensure that at least **one interface remains enabled**, otherwise you may lose access to the device. The interface names can be seen on the user interface as described in our handbook.