


Allgemeingültige Kundenzeichnung, aktueller Stand nur auf Anfrage  
General customer drawing, topical version only if required



$P = 15.00$  Pitch  
 $0.590"$  Raster  
 $D = 0.1.7 +0.1$   
 $0.066"$   
 $d = 1.24 \times 1.2$   
 $0.049" \times 0.047"$   
 $l = 5.0$   
 $0.197"$

12	165.00	6.496
11	150.00	5.905
10	135.00	5.314
9	120.00	4.724
8	105.00	4.133
7	90.00	3.543
6	75.00	0.952
5	60.00	2.362
4	45.00	1.771
3	30.00	1.181
2	15.00	0.590
n Poles	L1	L1
	Polzahl	[mm]
		[mm]


Cat. no.:

3 64092 04

Drawing no. . . . .

Issue no. . . . .

Sheet 01 of 01 sheets



 <b>General tolerance:</b> <b>DIN ISO 2768-mK</b>	96560/4 23.04.18 KRECHT_M		01
	Modification		
	Date	Name	
	27.10.2016	KRECHT_M	
	Responsible	SCHMITZ_T	
Scale: 5/1	Checked	HELIS_MA	
Supersedes: .	Approved	NOLTE_S	
		Product file: LUF 10.00	

**Weidmüller** 

Drawing no. . . . .

Issue no. . . . .

Sheet 01 of 01 sheets

**HO LUFS .../180**  
GEHÄUSE  
HOUSING

7412