

WEITERGABE SOWIE Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
Zuwendungen Verpflichten zu Schadenersatz. Alle Rechte fuer den Fall der Patent-, Gebrauchsmuster- oder Geschacksmustereintragung vorbehalten.
THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT AS WELL AS THE COMMUNICATION OF ITS CONTENTS TO OTHERS WITHOUT EXPLICIT AUTHORIZATION IS PROHIBITED.
OFFENDERS WILL BE HELD LIABLE FOR THE PAYMENT OF DAMAGES. WEIDMUELLER EXCLUSIVELY RESERVES THE RIGHT TO FILE FOR PATENTS, UTILITY MODELS OR DESIGNS.


MASSE OHNE TOLERANZ SIND KEINE PRUEFMASSE
DIMS. WITHOUT TOLERANCE ARE NOT CONTROL DIMS.

DIE DEUTSCHE VERSION IST VERBINDLICH
THE GERMAN VERSION IS BINDING


Technical Data

Rev.		
Materials		
Tape		polystyrene
colour		black
electrical properties		electric conductive
Cover Tape		
colour		polyester / polyethylene
electrical properties		transparent
		antistatic
Reel		
colour		polystyrene
electrical properties		black
		antistatic
System characteristic values		
Pitch / Row distance	mm	3.5 / 20
Solder pin length	mm	see order sheet
Downloads		
		www.weidmueller.de/...

Z 2/1




1/5



NO OF POLES MATSCHING IN TAPE														
OPEN ENDED					CLOSED ENDED					SOLDER FLANGE ENDED				
w					w					w				
32mm	44mm	56mm	72mm	88mm	32mm	44mm	56mm	72mm	88mm	32mm	44mm	56mm	72mm	88mm
4					4					4				
6					6					6				
8					8						8			
10						10					10			
	12					12					12			
	14					14					14			
	16					16						16		
	18					18						18		
		20					20					20		
		22					22						22	
		24					24						24	
			26					26					26	
			28					28					28	
			30					30						30
			32					32						32
				34					34					34
				36					36					36
				38					38					
				40										

ORDER NUMBERS SEE SHEET NO. 2

SHOWN: S2L-SMT 3.5/11/90°



For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to VDE 0110. The current-carrying capacity is to be determined according to DIN IEC 326 part 3. Weidmüller connectors are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the connectors are used to the intended purpose, all requirements with respect to the occuring of electrical, mechanical, thermic and corrosive stress will be satisfied.

TAPE AND REEL ACCORDING TO IEC 286-3 (EN 60286-3)

	80058/3 20.01.15 HELIS_MA 00		CAT.NO.: .	
	MODIFICATION		Weidmüller	
	DRAWN	26.11.2007	HELIS_MA	
	RESPONSIBLE		LANG_T	
	CHECKED	21.01.2015	HERTEL_S	
	APPROVED		LANG_T	
SCALE: 1/1		S2L-SMT 3.50/././90...RL		
SUPERSEDES: 3 33277/04		STIFTLISTE / TAPE PIN HEADER / TAPE		
		PRODUCT FILE: S2L-SMT 3.5		
		7272		