

Specification Text - Enclosure, Aluminium

45 mm x 50 mm x 30 mm ... 230 mm x 280 mm x 111 mm (Hight x Width x Depth)

Specification Text short:

Manufacturer: Weidmüller
Brand: Klippon®
Type: Terminal box, junction box, distribution box
Enclosure range: Klippon K
Material: Aluminium AlSi12
Lid: 4x captive fixing screws (Torx-Slot), hinge as option
Ambient temperatures: $-50\text{ °C} \leq T_{\text{amb}} \leq +135\text{ °C}$ (DIN EN 62208), including aging cycles


Specification Text long:

Manufacturer: Weidmüller
Brand: Klippon®
Type: Terminal box, junction box, distribution box
Enclosure range: Klippon K
Description: Klippon K61 VMQ
Article number: 1939700000
Material: Aluminium AlSi12
Manufacturing process: Die-cast aluminum.
Wall thickness: Enclosure base $\geq 3\text{ mm}$, Draft angle 1 to 2 ° / lid 3 mm
IP / NEMA Rating: IP66, IP 67, IP 68 (EN 62208, DIN EN 60529) / NEMA 4, 4X (UL 50E, CSA C22.2)
Surface: Natural
Dimensions (H x W x D): 160 mm x 260 mm x 91 mm
Lid: 4x captive fixing screws (Torx-Slot), hinge as option
Sealing for lid: Single (non-jointed) silicon O-ring with compression control, to prevent damage to the sealing gasket
Earth bolt: Internal: Srew connection / External: As option
Enclosure attachment: 4x captive fixing screws (Torx-Slot)
Ambient temperatures: $-50\text{ °C} \leq T_{\text{amb}} \leq +135\text{ °C}$ (DIN EN 62208)
Impact resistance: IK 09 (10 J) (DIN EN 50102)
EMC: Tested and based on VG95373-15:2004-07, methode KS 04B.
Determined shielding effectiveness is in average around 30 dB within the frequency range 100 to 1500 MHz

Specification Text - Enclosure, Aluminium

45 mm x 50 mm x 30 mm ... 230 mm x 280 mm x 111 mm (Hight x Width x Depth)

Klippon K61



Options:

Label fixing sets:	Stainless steel V4A / 316L / 1.4404, screwed or fixed by rivets. Punched silicon gasket with compression control for the label and its silicon gasket, to ensure the IP rating.
Mounting plates:	Galvanized sheet steel
Earth bolt:	Internal / external: M10 of stainless steel V4A / 316L / 1.4404 or M10 of brass or M6 of stainless steel V4A / 316L / 1.4404 or M6 of brass
Wall mounting brackets:	Set with 4 external brackets, stainless steel V2A / 304, 1.4301
Assembly of terminals:	All terminal blocks of type Klippon® Connect. All DIN rails vertical mounting, horizontal mounting as option. Terminal marker horizontal. Hazardous areas: All terminals for intrinsically safe circuits are colored blue, for non-intrinsically safe circuits are colored dark beige. On request: Assembly with control stations (switches, push buttons, lights, indicators).
Certifications:	For assembled resp. empty enclosures OIT Certification, Russia, Non-Containment, safety-related applications cULus Russian Maritime Register of Shipping

Specification Text - Enclosure, Aluminium**45 mm x 50 mm x 30 mm ... 230 mm x 280 mm x 111 mm (Hight x Width x Depth)****Weidmüller Interface GmbH & Co. KG**

Postfach 3030

32720 Detmold

Klingenbergstraße 16

32758 Detmold

Phone +49 (0) 5231 14-0

Fax +49 (0) 5231 14-292083

E-Mail info@weidmueller.comInternet www.weidmueller.com

You can find your local contact
on the internet at:

www.weidmueller.com/countries