

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Terminal blocks for copper conductors

Name and address of the applicant

Weidmüller Interface GmbH & Co. KG
Klingenbergstrasse 16,
32758 Detmold
Germany

Name and address of the manufacturer

Weidmüller Interface GmbH & Co. KG
Klingenbergstrasse 16,
32758 Detmold
Germany

Name and address of the factory

Note: When more than one factory, please report on page 2

☐ Additional information on page 2Weidmüller Interface GmbH & Co. KG
Klingenbergstrasse 16,
32758 Detmold
Germany

Ratings and principal characteristics

800/1000 V, 8 kV, 24 - 125 A, 2,5 - 35 mm²

Trademark (if any)

Weidmüller

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

SAK 2,5, SAK 2,5/35, SAK 4, SAK 4/35, SAK 6, SAK 6/35,
SAK 10, SAK 10/35, SAK 16, SAK 16/35, SAK 35, SAK 35/35, SAK 35/35/IK

Additional information (if necessary may also be reported on page 2)

☐ Additional information on page 2

-

A sample of the product was tested and found to be in conformity with

IEC 60947-7-1:2009

As shown in the Test Report Ref. No. which forms part of this Certificate

2228552.50 / 2228552.51 / 2228552.52 / 2228552.53 / 2228552.54 / 2228552.55

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051, NL-6825 MJ Arnhem, Netherlands