

Technical change to MultiCard in red

Dear Madam or Sir,

the products listed below are subject to a product change and will be supplied in a modified revision. Please pass this product information on to your employees and, if needed, to your customers. All modifications mentioned have been made to support our ongoing commitment to continual improvement and ongoing product development.

1. Initial situation


Our range of MultiCard markers with the fire classification V2 includes approx. 70 variants in the color red. There we use a polyamide PA66 which is a mixture of nature color raw material and a red colored batch.

2. Technical change

From now on we use only full colored polyamide PA66, so that a mixture is no longer needed.

- The function and printability of these markers are not affected.
- The color tone red does not change.
- Small deviations of up to 1mm are possible over the entire card length. This can easily be adjusted by the labelling software M-Print Pro.

Old and new version are visually identical -> Examples



3. Reason for change

In order to always be able to ensure a constant quality and color, only colored polyamide PA66 is used.

4. Availability

From week 19/2020, new MultiCard markers in red will only be made with the new material. Batches with the old material will be sold out.

5. Affected parts

All MultiCard variants in the color red and fire class V2 are affected. The list with all article numbers is attached.

6. Data

- PCN-number : PCN-PKD80-20200512-00-A
- Date of publishing : 13.05.2020
- Duration of validity : unlimited
- Revision number : none

We hope that the changes will benefit your business and will not affect you in any significant way and apologise in case of any inconvenience caused. Please rest assured that we will do everything possible to achieve this product change as smoothly as possible with minimum or no business disruption.

For further questions or if you need any additional assistance or information, please contact your local sales office directly. All contacts for sales representatives are available here: <http://www.weidmueller.com/contact>

Details of this and any other product changes can also be found on our web page by following the link shown below

<http://www.weidmueller.com/int/service/online-support-and-downloads/product-change-notification>

Best regards

Product Management

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16, 32758 Detmold, Germany

Weidmüller – Your partner in Industrial Connectivity
We look forward to sharing ideas with you – **Let's connect.**

Article list for PCN-PKD80-20200512-00-A

Art. no.	Type	Art. no.	Type
1609801686	DEK 5/5 MC NE RT	1919530000	SF 3/12 MC NE RT V2
1238320000	DEK 5/6 MC NE RT	1918900000	SF 3/21 MC NE RT V2
1773531686	WS 10/5 MC NE RT	1919010000	SF 4.5/21 MC NE RT V2
1917440000	WS 10/6 MC M NE RT	1919570000	SF 4/12 MC NE RT V2
1773541686	WS 12/5 MC NE RT	1919070000	SF 4/21 MC NE RT V2
1773551686	WS 12/6 MC NE RT	1919640000	SF 5/12 MC NE RT V2
1773561686	WS 12/6.5 MC NE RT	1919130000	SF 5/21 MC NE RT V2
1773521686	WS 8/5 MC NE RT	1919180000	SF 6/21 MC NE RT V2
1539980000	PM 2.7/2.6 MC NE RT	1852370000	SFX 10/23 MC NE RT V2
1317270000	MF 10/8 MC NE RT	1248830000	SFX 10/60 S MC NE RT
1924260000	MF-W 5/5 MINI MC NE RT	1963650000	SFX 11/60 MC NE RT
1559920000	ESG 9/20 MC NE RT	1852420000	SFX 14/23 MC NE RT V2
1026570000	ESG X20 10/7 MC NE RT	1369550000	SFX 30/60 MC NE RT
1001170001	ESG X20 MC NE RT	1852470000	SFX 9/24 MC NE RT V2
1906120000	SM 27/18 K MC NE RT	1323470000	SFX 9/24 S MC NE RT
1906110000	SM 27/18 MC NE RT	1248780000	SFX 9/40 S MC NE RT
1288320000	CC 15/17 K MC NE RT	1813150000	SFC 0/12 MC NE RT
1288330000	CC 15/27 K MC NE RT	1813200000	SFC 0/21 MC NE RT
1288380000	CC 15/49 K MC NE RT	1813250000	SFC 0/30 MC NE RT
1288340000	CC 15/60 K MC NE RT	1747320003	SFC 1/12 MC NE RT
1085430000	CC 30/60 K MC NE RT	1779080003	SFC 1/21 MC NE RT
1158830000	CC 30/60 O4MM MC NE RT	1805740000	SFC 1/30 MC NE RT
1288390000	CC 85/54 K MC NE RT	1062020000	SFC 2.5/12 MC NE RT
1208420000	CC 85/54 MC NE RT	1062080000	SFC 2.5/21 MC NE RT
1434110000	CC DIA 30/3.5 MC NE RT	1758320003	SFC 2/12 MC NE RT
1718411686	TM-I 12 MC NE RT	1805790000	SFC 2/21 MC NE RT
1421170000	TM-I 12/18 MC NE RT	1805850000	SFC 2/30 MC NE RT
1609981686	TM-I 15 MC NE RT	1025240000	SFC 3/12 MC NE RT
1718431686	TM-I 18 MC NE RT	1025290000	SFC 3/21 MC NE RT
1680411686	TM-I 20 MC NE RT	1025330000	SFC 3/30 MC NE RT
1428510000	TM-I 23 MC NE RT		
1876380000	TM-I 30 MC NE RT		
1714101686	VT-TM-I 18 MC NE RT		
1919230000	SF 0/12 MC NE RT V2		
1918490000	SF 0/21 MC NE RT V2		
1919280000	SF 00/12 MC NE RT V2		
1918570000	SF 00/21 MC NE RT V2		
1919320000	SF 1/12 MC NE RT V2		
1918600000	SF 1/21 MC NE RT V2		
1919460000	SF 2/12 MC NE RT V2		
1918670000	SF 2/21 MC NE RT V2		