

**8000081272 PV combiner box thermal report****PV 208S0F3CXXV0O0TXPX15LWW****INPUT DATA**


Enclosure model	636 x 847 x 300 mm
Number of MPPT	1
Switch-disconnector model (per MPPT)	400A 1500V
Maximum current (per MPPT)	193 A
Number of inputs (per MPPT)	6
Fuse-link model	50A gPV 1500V 22x58mm
Number of monitoring devices (per MPPT)	0
Type of mounting	Against wall, all other sides detached
Maximum allowed internal temperature	70 °C
Combined inputs	1
Height (A)	636 mm
Width (B)	847 mm
Depth (C)	300 mm
Effective cooling surface $A_e$ of the enclosure	1.45 m <sup>2</sup>

**RESULTS**

Ambient temperature (no direct sunlight)	35 °C
Rated current per input at 35°C	32.10 A
Power dissipated by components (except wiring)	67 W
Power dissipated by wiring	20 W
Total dissipated power	87 W
Temperature rise, mid height	15 °C
Temperature rise, top	19 °C
Internal temperature, top	54 °C

**CURRENT RATINGS**

At 35°C	32.10 A
At 40°C	32.10 A
At 45°C	32.10 A
At 50°C	32.10 A

**NOTES**

Thermal report based on IEC TR 60890 ed2.0

Thermal report does not include the direct sunlight effects