

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switching Power Supply

Name and address of the applicant

Weidmüller Interface GmbH & Co. KG
Klingenbergstr. 26
32758 Detmold, Germany

Name and address of the manufacturer

Weidmüller Interface GmbH & Co. KG
Klingenbergstr. 26
32758 Detmold, Germany

Name and address of the factory

See additional page(s)

Ratings and principal characteristics

Input : 100-240VAC, 50/60Hz, 2.0-1.0A; Class I
Output: 1) 5VDC, 14A; 2) 12VDC, 6A; 3) 24VDC, 3A

Trademark (if any)

Weidmüller

Customer's Testing Facility (CTF) Stage used

N/A

Model / Type Ref.

1) PRO MAX 70W 5V 14A 2) PRO MAX 72W 12V 6A
3) PRO MAX 72W 24V 3A

Additional information (if necessary may also be reported on page 2)

For model differences, refer to the test report.
Re-issue of JPTUV-102219-M1 dated 31.05.2023,
due to first amendment.

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014
See Test Report for National Differences

As shown in the Test Report Ref. No. which forms part of this Certificate

50304899 003

This CB Test Certificate is issued by the National Certification Body


TÜV Rheinland Japan Ltd.
Global Technology Assessment Center
4-25-2 Kita-Yamata, Tsuzuki-ku
Yokohama 224-0021, Japan
Phone + 81 45 914-3888
Fax + 81 45 914-3354
Mail: info@jpn.tuv.com
Web : www.tuv.com



Date: 2023-12-28

Signature:

Sommy Chen