

**INSTALLATION INSTRUCTIONS**  
**& CONDITIONS FOR SAFE USE**

Ex eb IIC Gb

**Modular TERMINAL Blocks: SAKK- Series****TÜV 18 ATEX 8208 U****IECEx TUR 18.0018 U****Notified Body No. of Ex - QA: 0344****Label print on package unit: 0344**

## Standards:

EN IEC 60079-0:2018 and EN IEC 60079-7:2015 A1:2018  
IEC 60079-0: 7th Edition and IEC 60079-7: 5.1th Edition**Modular Terminal Blocks: SAKK 10**

Version:			Order No
	SAKK 10		9502610000
	SAKK 10 KER/WS		1598090000
Accessories:	Type		
end plate	AP SAKK4/10 KER/WS		9502630000
end bracket	MEW 1/32		0445600000
Terminal rail	TS 32/... acc.to IEC 60715		
Cross-connection	Cross-connection link	QL 2 SAKK10 QL 3 SAKK10 QL 4 SAKK10 QL 10 SAKK10	9502650000 9502660000 9502670000 9502680000
	Connecting sleeve	VH 12.5 SAKK10	9502690000
	Fixing screw	KISC M3X20.5/10 EK4	0303000000

**Insulation material:**




- Type	Ceramic
- Tracking resistance (A) to IEC 60112	CTI ≥ 600
- Flammability class to UL 94	V0
- Operating temperature range	-60°C to +210°C (insulating material limit)
- Ambient temperature range	-60°C...+40°C (for T6 applications)
- Ambient temperature range	-60°C...+55°C (for T5 applications)
- Ambient temperature range	-60°C...+95°C (for T4 applications)
- Ambient temperature range	-60°C...+155°C (for T3 applications)
- Ambient temperature range	-60°C...+170°C (for T2 applications)

**Technical data according to IEC/EN 60079-7 (increased safety "eb"):****SAKK 10**

- Rated voltage	440 V
- Rated current	57 A
- Temperature rise with rated current	$\leq 40 \text{ K} / 57 \text{ A}$
- Rated current with cross connection	57 A
- Contact resistance with rated conductor SAKK 10 KER/WS (TIN)	0,2 m $\Omega$
- Contact resistance with rated conductor SAKK 10 (Nickel)	0,3 m $\Omega$
- Conductor cross section solid	1,5 - 16 mm $^2$
- Conductor cross section flexible	2,5 - 16 mm $^2$
- Conductor cross section strained	16 mm $^2$
- cross section, American Wire Gauge	14 - 6 AWG
- Tightening torque range, terminal screw	2 - 2,4 Nm
- Tightening torque range for cross connection	0,5 - 1,0 Nm
- Stripping length	12 mm

**IECEx / ATEX Terminal and Cross-Connection Arrangements:**

**Max voltage data according to IEC/EN 60079-7 in conjunction with  
protective earth terminal blocks of the SAKK-Series, (increased safety "eb"):**

**Application Case****A - Continuous****C - Adjacent – separated by an end plate****D - Intermediate - bridging one or more unconnected terminals**

Information for further cross-connector arrangements will be provided on request.

**Note:**

If smaller cross sections than the rated cross section are used, the belonging lower current has to be laid down in the IECEx/EC-Type Examination Certificate of the complete apparatus.

**Mounting instructions:**

Regarding the use of accessories the instructions of the manufacturer must be followed.

**Schedule of Limitations:**

The SAKK-series products are suitable for use in enclosures in atmospheres with flammable gases or combustible dust. For flammable gases these enclosures must satisfy the requirements according to EN 60079-0 and EN 60079-7. For combustible dust the enclosure must satisfy the requirements according to EN 60079-0 and EN 60079-31.

The enclosure shall be constructed to block all sun and UV light from affecting the terminal blocks. The terminal blocks shall be placed inside a suitable certified IP54 enclosure in type of protection "eb" for gas atmosphere. For dust atmosphere the terminal blocks shall be mounted inside a suitable certified enclosure (EN60079-31) in type of protection "t".

Under normal operating conditions the temperature rise of the terminal blocks is maximum 40 K, measured at the maximum permitted rated current. Due to the above mentioned, the terminal blocks may be used in apparatus of temperature classes T6..T1 as long as the terminal block ambient temperature range is not exceeded. No part of terminal block must exceed 210°C under any condition.

**Ambient temperature**

T6 (- 60°C ... +40 °C)

T5 (- 60°C ... +55 °C)

T4 (- 60°C ... +95 °C)

T3 (- 60°C ... +155 °C)

T2 (- 60°C ... +170 °C)

When using the SAKK-series products especially with other terminal blocks series or sizes or accessories the requirements for clearance and creepage distances according to table 2 of EN 60079-7 must be observed. Regarding the use of covers, cross-connectors and end brackets the instructions of the manufacturer must be followed.

For cross connection accessories current rating, resistance across the terminal please refer to the table under "technical data" above.

No other wire sizes or types than the ones specified in instructions must be used. The terminal blocks must either be mounted next to another block of the same type and size or with an end plate.

If smaller conductor cross sections than the rated conductor cross sections are used, then the corresponding lower current shall be stated in the Certificate of the complete apparatus.

Unused terminals shall be tightened.

**Essential Health and Safety Requirements:**

Concerning ESRs this Schedule verifies compliance with the Annex III of ATEX directive only. By placing the product on the market, the manufacturer declares compliance with other relevant Directives, and all other safety related requirements including those of Annex II of this Directive.